



Product data sheet

Power tools for trade & industry

Radio

GPB 18V-5 SC



Play it loud: powerful top performer for digital radio on rough jobsites

The most important data

Input voltage(s), battery	18 V
Input voltage(s), mains	100 – 240 V
Radio frequency range FM	87.5 – 108 MHz

Part Number 0 601 4A4 170

[> More product information](#)

Technical data

Technical data

Radio frequency range FM	87.5 – 108 MHz
Radio frequency range DAB+	174.928 – 239.2 MHz
Station presets FM	4
Station presets DAB+	4
Input voltage(s), battery	18 V
Input voltage(s), mains	100 – 240 V
Weight excl. battery	8.8 kg
Rated power of amplifier (in mains operation)	40 W
Packaging dimensions (width x length x height)	366 x 385 x 362 mm
Plug Type	Type G

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Highly flexible sound entertainment: digital (DAB+; Bluetooth®), conventional radio reception (FM) and AUX
 - Outstanding level of robustness: protective roll cage; designed to withstand harsh jobsite conditions
 - Crystal clear, massive sound: four speakers with 20 W (5 W each), integrated subwoofer (20 W) for powerful bass response
-

