

Features

- Heavy duty industrial cable reel with spring load.
- High quality engineer PP housing .
- Input line: H07RN-F,3G1.5mm²,2m length (1.88m net cable length,0.12M cable inside cable reel) . Output line: H07RN-F,3G1.5mm²,11m length (10.75m net cable length,0.25M cable inside cable reel) . Pull the power cords and stop any location as you want,each stop was around 50cm.
- Wall bracket 180 degree swivel.
- Over current or temperature protector.

RS PRO Automatic cable reel H07RN-F 3G1.5mm² 11(10.75+0.25)+2(1.88+0.12)m

RS Stock No.: 171-7880



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *A silver plated copper shielding coating designed to give low resistance even in thin layers on plastic electronic housing.*

Electrical Specifications

Rated voltage	230 V ac 50Hz
Rated power (Full-reeled)	1000W
Rated power (Unreeled)	2300W
Re-settable thermal protection	@56+/-5oC