



ENGLISH

Datasheet

# RS Pro Conduit Through Box



## Specifications:

Stock No:	471-1243
Material:	316 - V4A Stainless Steel
Finish:	Satin (Lid), Electropolished (Base)
Conduit Ø (mm):	20
Conduit Box Ø (mm):	60.3
Compatible With:	Metric Conduit
Gasket Material:	2mm Neoprene Rubber
Rating:	IP67
	DIN VDE 0470 TEIL 1/11.92
	BS EN 60529 : 1992
	IEC 529 : 1989
	UL Approved
Thread Type:	Metric / Female
Thread Details:	ISO form 1.5mm pitch