


Part Number : [688014593](#)

Product Description : Flexi-Mate-to-Flexi-Mate Cable Assembly, LED Board-to-Board Application, Cable Length 46.00mm, 2 Circuits

Series Number : 68801

Status : Obsolete


Product Category : Power and Signal Cable Assemblies



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Power and Signal Cable Assemblies
Series	68801
Description	Flexi-Mate-to-Flexi-Mate Cable Assembly, LED Board-to-Board Application, Cable Length 46.00mm, 2 Circuits
Application	Board-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Flexi-Mate-to-Flexi-Mate
Product Name	Flexi-Mate
UPC	887191406381

Electrical

Voltage - Maximum	500V
-------------------	------

Physical

Cable Length	46.00mm
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	White
Gender	Female-Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Resin	Polyester
Net Weight	1.100/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	3.70mm
Single Ended	No
Wire/Cable Type	UL 11047
Wire Size (AWG)	24

Mates With / Use With

Mates with Part(s)

Description	Part Number
Flexi-Mate Board-to-Board/Wire-to-Board Receptacles	<u>503471</u>

This document was generated on Aug 11, 2025

Obsolete