

Surface Socket Outlet



Options available

- Less Enclosure - add LE to catalogue number e.g. 56SO410 becomes 56SO410LE.
- Resistant Orange - add RO to catalogue number e.g. 56SO410 becomes 56SO410,RO.
- Resistant White - add RW to catalogue Number e.g. 56SO310 becomes 56SO310RW.

Extra Low Voltage and 3 Phase sockets

Clipsal Surface Socket Outlets range in size from 32V 10A to 500V 50A.

All sockets feature hoseproof and dust resistant flaps with automatic snap catch latches. The transparent flap enables instant visual inspection of socket condition and pin configuration.

The full range of sockets accommodate both the superseded IP56 plain plugs and the current IP66 retention ring plugs in order to rationalise the number of variations required.

Earth and neutral connectors accommodating 3 x 6mm² cable are supplied with all 500V models.

Terminal housings are moulded in tough polyester to minimise damage.

| Catalogue Number | I_n (Amp) | U_i / U_o (Volt) | Number of Sockets | Cond. Term Size In mm | | IP Rating | O/A Dims. (H) x (W) x (D) | Matching Plug Straight | Matching Plug Straight | Socket Config. |
|------------------|-------------|--------------------|-------------------|-----------------------|-----------|-----------|---------------------------|------------------------|------------------------|----------------|
| | | | | Min. | Max/Cond. | | | | | |
| 56S0310 | 10A | 250V | 3 Flat | 1.5 | 6 | 66 | 107x101x77 | 56P310 | | A |

Dimensional Drawings

