

Maintenance workbench – 6 drawers, wooden top, 2 m



Description:

- 6 drawers unit: - 3 drawers 60 mm.
- 2 drawers 130 mm. - 1 drawer 200 mm.
- The drawers can be fitted with thermoshaped and foam modules
Maximum load resistance per drawer : 20/25/30 kg.
- Polypropylène drawer pulls with safety hooks.
- Lock on side to reduce the risk of damage. Centralized locking system, delivered with 2 keys, one folding.
- Leg: - Steel sheet « U » profile. - Arranged for ground fixing.
- Worktop: - 40 mm multilayered beech wood. - Suitable for installing a vice. - Spread load resistance: 1 ton.
- Accessories: - Integrated holder for cans or bottles (Free positioning on right or left). - Sides of the drawer unit are perforated to receive most of the JET.XL accessories range. - Metal partitions can be provided in option (JET2.15 for 60 mm drawers and JET2.16 for 130 mm drawers).
- Easy and fast assembly.
- Overall dimensions (L. x D. x H.): L2000*D700*H816 mm.
- Drawer useful size: L.569 x D.421 x H.60 / 130 / 200 mm.

|  | Depth [mm] | Length L [mm] | Height H [mm] |
|----------------------------------------------------------------------------------|------------|---------------------|---------------------|
| 2000.ROLL6M3W | 700.0 | 2000.0 | 850.0 |