

PREVOST FILTRATION - UNIT COMBINATIONS

Filter-regulator lubricator with manual valve and dry outlet - 4 units



Part number	Female thread	Flow rate at 6.00 bar (l/min) ($\Delta P = 1.00$ bar)	Max. operating pressure (bar)	Filtration (μm)	Net weight (Kg)
ATU VBD2585100	G1/8	400.00	10.00	25.00	0,79
ATU VBD2585101	G1/4	700.00	10.00	25.00	0,79
ATU VBD2585102	G3/8	2000.00	10.00	25.00	3,046
ATU VBD2585103	G1/2	3300.00	10.00	25.00	2,55