



Product data sheet

Power tools for trade & industry

Cordless Circular Saw

PRO GKS 18V-68-2



Faster, Stronger, Safer – The Lightweight Cordless Circular Saw that enhances efficiency

The most important data

Battery voltage	18.0 V
Saw blade diameter	190 mm
No-load speed	5,225 – 5,775 rpm

Part Number 0 601 6D0 001

Technical data

Technical data

No-load speed	5,225 – 5,775 rpm
Saw blade diameter	190 mm
Saw blade bore diameter	30 mm
Weight excl. battery	3.5 kg
Battery voltage	18.0 V
Packaging dimensions (width x length x height)	360 x 444 x 253 mm
BITURBO	No

Noise/vibration information

Wood sawing

Vibration emission value ah	0.9 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Easily cuts through tough materials thanks to enhanced overload capacity
- Boosts workload efficiency thanks to superior cutting speed
- Keeps you safe with KickBack Control system
- Lights up dark work areas with convenient LED light



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

