



PRODUCT DATASHEET

Datasheet creation date: 2025/06/02 9:11 (UTC)



6806DD

Single-Row Deep Groove Ball Bearings

Boundary Dimensions

d	30	mm	Bore diameter
D	42	mm	Outside diameter
B	7	mm	Width
r (min.)	0.3	mm	Chamfer dimension

Basic Load Ratings

Cr	5200	N	Basic dynamic load rating
C0r	3650	N	Basic static load rating

Speeds

Grease	9000	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	32	mm	Diameter of shaft abutment
da (max.)	32	mm	Diameter of shaft abutment
Da (max.)	40	mm	Diameter of housing abutment
ra (max.)	0.3	mm	Radius of shaft or housing fillet

Calculation factors

fo	16.4		Factor
----	------	--	--------

Additional information

z	18		Number of Balls
Dw	3.5	mm	Ball Diameter

Mass

Mass approx.	0.024	kg	Mass approx.
--------------	-------	----	--------------

