



Product data sheet

Power tools for trade & industry

Cordless Press Tool

PRO GPT 18V-32



For a large variety of diameters, the 18 V press tool with the power of 32 kN

The most important data

Pressing force max	34 kN
Comp range dia max plastic	110 mm
Comp range dia max metall	54 mm

Part Number 0 601 9M2 100

Technical data

Description

Product category subdivision	Cordless Press Tool
Head rotation	360 °
Pressing force max	34 kN
Time pressing cycle	5 s
Comp range dia max metall	54 mm
Comp range dia max plastic	110 mm
Calibration Interval	40.000 cycles
BITURBO	No
Weight	3.4 kg
Weight excl. battery	3.4 kg

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Power of 32 kN for a large variety of diameters, yet easy to manoeuvre in tight spaces
- Fast, comfortable working – pressing cycles take less than 5 seconds
- Convenient and robust thanks to the battery protection cover

