



## OUR OFFER

### EATON – PowerXL DE1

## PowerXL DE1 Variable Speed Starter

Fast and error-free installation  
Commissioning Out-Of-The-Box (time savings up to 70%)  
Easy change from a motor starter  
No special drive skills or knowledge required  
Reduced efforts on technical support  
Integrated motor protection and short-circuit protection  
Compact side-by-side and horizontal mounting  
Lower cooling expenses (due to high permissible ambient temperatures)  
With integrated EMC filter  
IP20 Protection Class



### Variable Speed Starter

Stock-No.	Eaton MPN	Power Rate	Output Voltage	Output Current
820-3541	DE1-121D4FN-N20N	0.25 kW	230 V ac	1.4 A
820-3550	DE1-122D3FN-N20N	0.37 kW	230 V ac	2.3 A
820-3553	DE1-122D7FN-N20N	0.55 kW	230 V ac	2.7 A
820-3557	DE1-124D3FN-N20N	0.75 kW	230 V ac	4.3 A
820-3566	DE1-127D0FN-N20N	1.5 kW	230 V ac	7 A
820-3569	DE1-129D6FN-N20N	2.2 kW	230 V ac	9.6 A
820-3563	DE1-341D3FN-N20N	0.37 kW	400 V ac	1.3 A
820-3572	DE1-342D1FN-N20N	0.75 kW	400 V ac	2.1 A
820-3575	DE1-343D6FN-N20N	1.5 kW	400 V ac	3.6 A
820-3579	DE1-345D0FN-N20N	2.2 kW	400 V ac	5 A
820-3588	DE1-346D6FN-N20N	3 kW	400 V ac	6.6 A
820-3581	DE1-348D5FN-N20N	4 kW	400 V ac	8.5 A
820-3585	DE1-34011FN-N20N	5.5 kW	400 V ac	11.3 A
820-3594	DE1-34016FN-N20N	7.5 kW	400 V ac	16 A

### Accessories

Stock-No.	Eaton MPN	Description
820-3597	DE-EXT-SET	DE1 Parameterization Module
786-3527	DX-COM-STICK	Parameter Copy Stick
786-3514	DX-KEY-LED	Remote Display



For more technical information please visit:  
[www.rs-online.com](http://www.rs-online.com)