

Datasheet

70 W Fluorescent, Ceiling Light, Batten, 1 Lamp, Anti-corrosive

Stock Number: 712-4112, 712-4055, 712-4043, 712-4100



Indoor lighting Fluorescent battens and diffusers

The range of fluorescent battens from GET is the ideal choice for commercial, industrial or domestic installations – combining quality, style, ease of installation and value for money.

- High impact moulded lamp holder end cap assemblies
- Powder coated steel casing for durability and enhanced rigidity
- High temperature cable for electrical safety
- High quality starter for reliability and long life
- Large terminal connectors and cable entry for ease of wiring
- Approved ballasts for long operational life and low noise emissions
- Easy fit cover tray, simply turn the twist lock at each end of the batten for fuss free installation and maintenance without the use of a tool
- High quality long life power factor correction capacitor (HPF versions)
- Integral 3 hour battery back up (Emergency versions)

Square diffusers


LPSK136



LPSK258

Code	Description	Qty
LPSK118	650mm (2ft) single	2
LPSK218	650mm (2ft) twin	2
LPSK136	1225mm (4ft) single	2
LPSK236	1225mm (4ft) twin	2
LPSK158	1525mm (5ft) single	2
LPSK258	1525mm (5ft) twin	2
LPSK170	1790mm (6ft) single	2
LPSK270	1790mm (6ft) twin	2

- Prismatic acrylic diffuser for low glare soft light
- No special tooling required for installation and maintenance
- Includes lipped cover tray for snug fit which minimises insect ingress and reduces routine cleaning
- UV stabilised high impact end caps which do not allow light to penetrate

Bare batten - low power factor (complete with lamp)


LP236LPF

Code	Description	Wattage	Qty
LP118LPF	650mm (2ft) single	18W	1
LP218LPF	650mm (2ft) twin	18W	1
LP136LPF	1225mm (4ft) single	36W	1
LP236LPF	1225mm (4ft) twin	36W	1
LP158LPF	1525mm (5ft) single	58W	1
LP258LPF	1525mm (5ft) twin	58W	1
LP170LPF	1790mm (6ft) single	70W	1
LP270LPF	1790mm (6ft) twin	70W	1

- Supplied with white 35 T8 fluorescent tubes
- Durable slim line steel construction
- Width of base 54mm
- Simple 90° turn twist toggles allow for easy access to the gear tray without the need for tools
- Large terminal blocks for fast and easy cable connection

Bare batten - high power factor (complete with lamp)


LP118HPF

Code	Description	Wattage	Qty
LP118HPF	650mm (2ft) single	18W	1
LP218HPF	650mm (2ft) twin	18W	1
LP136HPF	1225mm (4ft) single	36W	1
LP236HPF	1225mm (4ft) twin	36W	1
LP158HPF	1525mm (5ft) single	58W	1
LP258HPF	1525mm (5ft) twin	58W	1
LP170HPF	1790mm (6ft) single	70W	1
LP270HPF	1790mm (6ft) twin	70W	1

- High quality epoxy powder coated finish
 - UV stabilised, non colouring, high impact end cap assemblies
 - End cap knockouts - no special tool or end cap drilling required
 - Low and high power factor battens for general use
 - Emergency available to order (high power factor only)
- Volts: 240V

