





Main

Range	PrismaSeT Active
Range of product	PrismaSeT G Active
Product or component type	Canopy
Accessory / separate part category	Enclosure accessory
Range compatibility	PrismaSeT PrismaSeT G Active enclosure
IP degree of protection	IP41

Complementary

Installation description	2 floor-standing enclosure + duct - width 600 + 600 + 300 mm 2 wall-mounted enclosure + duct - width 600 + 600 + 300 mm
Quantity per set	Set of 1
Height	45 mm
Width	1500 mm
Depth	280 mm
Net weight	6.32 kg
Surface finish	Matt Textured
Material	Treated sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration