

# Specifications for BMP51 Label Printer Labels

|                               |  |
|-------------------------------|--|
| <b>Adhesive</b>               | Permanent Acrylic  |
| <b>Article No.</b>            | 143283   |
| <b>Brady Material No.</b>     | <a href="#">B-432</a>  |
| <b>Material Type</b>          | Polyester  |
| <b>Colour</b>                 | Black on Clear   |
| <b>Finish</b>                 | Gloss  |
| <b>Order Reference</b>        | M-78-432-CL-BK   |
| <b>Printer Compatibility</b>  | BMP51; BMP53   |
| <b>Size - Height (mm)</b>     | 48.26  |
| <b>Size - Width (mm)</b>      | 25.40  |
| <b>Additional Information</b> | Designed for powder coated surfaces; Good moisture resistance; High adhesion |
| <b>Thickness (mm)</b>         | 0.1016   |
| <b>Total Qty per Pack</b>     | 100 Label(s) / Box   |
| <b>Approval/Compliance</b>    | UL Recognised; CSA Accepted  |
| <b>Brand</b>                  | ToughBond™ Series  |
| <b>Application</b>            | Laboratory Identification; Product Identification                            |
| <b>Environment</b>            | Freezer; Autoclave   |
| <b>Industry</b>               | Laboratory; Healthcare   |
| <b>Laboratory Application</b> | General Identification   |
| <b>Max. Service Temp. °C</b>  | 100  |
| <b>Min. Service Temp. °C</b>  | -40  |
| <b>Software</b>               | LabelMark  |
| <b>Surface</b>                | For smooth & textured/rough surfaces   |