

18V Hedge Trimmer 60cm BL LXT

DUH601Z

Brushless hedge trimmer powered by single 18V Li-ion battery.



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	18 v
Blade Length	600 mm
Blade type	Double Sided
Max Branch Diameter	21.5 mm
Strokes per Minute	0 - 2,000 / 0 - 3,600 / 0 -4,400 spm
Net weight	3.8 - 4.5 kg
Noise sound pressure	82 dB(A)
Noise sound power	95 dB(A)
Noise K factor	3 dB(A)
Vibration	2.5 m/sec ²
Vibration K factor	1.5 m/sec ²

USER BENEFITS

- New triple-edged cutting teeth are designed to easily catch and firmly hold branches. Curved blades reduce friction resistance to suppress energy loss. Due to the low resistance run time is increased.
- Brushless motor
- Variable speed control (3-speed + trigger)
- Constant speed control
- Electric brake
- 5 position rotating rear handle
- Soft start
- Ergonomic soft grip
- Reverse button
- Equipped with Battery protection circuit: designed to protect the battery from damages due to overdischarge, high temperature or overload current.

[Link to product - makitauk.com](https://www.makita.com)



RELATED PRODUCTS

(Reco

■ OTHER