

9050 // VISION PROTECT

Full-vision goggles
PPE risk category II



Scratch-resistant
Resistance to fogging
Excellent field of vision



9050 // VISION PROTECT



Frame:	PVC, grey / black
Oculars:	Polycarbonate, transparent
Size(s):	One size
Packaging unit:	120 piece(s)
Certification:	EN 166

NITRAS VISION PROTECT, full-vision goggles, frame grey / black, oculars transparent (colour code: 1412), clear shade, resistant to fogging, scratch-resistant, ultraviolet filter, good colour recognition, intended for long-term use, flexible and length-adjustable headband, optimal ventilation openings, large panoramic lens for an excellent field of vision, perfect wearing comfort, suitable for wearer of glasses, PPE risk category II

EN 166
AS EN 166 3 9 BT
AS 1 BT 9 KN



Industries

-  Craft
-  Building / Construction
-  Automotive manufacturing
-  Waste management
-  Wood processing
-  Chemistry / laboratory

Advantages

- + Scratch-resistant
- + Resistance to fogging
- + Excellent field of vision



Further images



Performance values

EN 166:2001	Test parameter	Performance levels	Test result
AS EN 166 3 9 BT	Frame marking	-	AS EN 166 3 9 BT
AS 1 BT 9 KN	Oculars marking	-	AS 1 BT 9 KN

Additional information

Miscellaneous

Thickness oculars (approx.)	2 mm
Weight (approx.)	87 g

Logistics data

Colour code	GTIN (SPU)	GTIN (PU)	Length (m)	Width (m)	Height (m)	Weight (kg)	Quantity PU / pallet
1412	4059904223707	4059904223714	0,53 m	0,78 m	0,45 m	17 kg	

Customs tariff number: 90049010000

Country of origin: Malaysia