



PRODUCT-DETAILS

SPL16/M20/A**STR NPB FITTING M20 16MM-MET****General Information**

Extended Product Type	SPL16/M20/A
Product ID	7TCA296030R0103
EAN	5020963001307
Catalog Description	STR NPB FITTING M20 16MM-MET
Long Description	Nickel Plated Brass Liquid Tight Straight Fitting with Fixed External Threads, Nominal Conduit Size 16 Millimeters, Metric Thread Size M20

Additional Information

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

Ordering

EAN	5020963001307
UPC	786210245881

Technical

Number of Batteries	0
Color	Metallic
Material	Brass
Size	3/8 Inch

Environmental

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963001307
Package Level 1 Height	7.87 in 200 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	5.9 in 150 mm

Certificates and Declarations

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

External Classifications and Standards

ETIM 8	EC001180 - Screw connection for protective metallic hose
ETIM 9	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

