

General Information

Extended Product Type:	232RPR6
Product ID:	2CMA168283R1000
EAN:	7392696682831
Catalog Description:	Socket-outlet with RCD, 6h, 30mA, 32A, IP44, 2P+E
Long Description:	Socket-outlet with RCD, earthing sleeve position 6h, 30mA, rated current 32A, IP44 splash proof, 2-poles+earth, frequency 50-60 Hz, color code Blue

Additional Information

Additional Information:	Cable entry, knock-outs 2xØ25mm
Cable Cross-Section:	2.5 ... 10 mm ²
Cable Entry Position:	Top
Cable Outlets Per Side:	2xØ25
Color:	Blue
Country of Origin:	Czech Republic (CZ)
Customs Tariff Number:	85366990
Data Sheet, Technical Information:	2CMC700014C0008
Declaration:	2CMC700005D0001
Declaration of Conformity - CE:	2CMC700005D0001
Degree of Protection:	acc. to IEC 60529 IP44
E-nummer:	2466304
EAN:	7392696682831
ETIM 4:	EC001324 - CEE socket outlet, disconnectable, with fuse
ETIM 5:	EC001321 - CEE socket outlet
ETIM 6:	EC001321 - CEE socket outlet
Enclosure Material:	Thermoplastic
Environmental Information:	2CMC700001D0002
Frequency (f):	60 Hz
Function:	Surface socket outlet with RCD, 30 mA
Gross Weight:	1.19 kg
Housing Material:	Thermoplastic (PBT)
IIT Publishing Status:	Level 0 - Information enabled
Instructions and Manuals:	2CMC700002D0001
Invoice Description:	Ind. P&S#232RPR6
Minimum Order Quantity:	1 piece
Number of Poles:	3
Number of RCD 30mA:	1
Number of RCDs:	1
Object Classification Code:	2CMT005069
Package Level 1 EAN:	7392696682831
Package Level 1 Gross Weight:	1.3 kg
Package Level 1 Height:	265 mm
Package Level 1 Length:	120 mm
Package Level 1 Units:	1 piece
Package Level 1 Width:	152 mm
Product Main Type:	CRPR

Product Name:	Industrial Socket Outlet with Protection
Product Net Depth:	243 mm
Product Net Height:	243 mm
Product Net Length:	149 mm
Product Net Weight:	1.2 kg
Product Net Width:	120 mm
Protection Type:	Splashproof
Rated Current (I_n):	32 A
Rated Residual Current:	30mA
Rated Voltage (U_r):	200 ... 250 V
RoHS Date:	L23
RoHS Information:	2CMC700057D0001
RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1
Selling Unit of Measure:	piece
Short Description:	Socket-outlet with RCD, 6h, 30mA, 32A, IP44, 2P+E
Size:	149X120X243
Standards:	IEC 60309-1 IEC 60309-2
Suitable For:	Socket Outlets with RCD
Suitable for Product Class:	Industrial Plugs and Sockets
UNSPSC:	39120000
Clock Position Of Grounding Contact:	6 hour

