













# tube polyuréthane souple calibré




## 1025U tube polyuréthane polyester souple, rouleau de 25 m

Ø ext. tube mm	Ø int. tube mm	R rayon minima de courbure à 20° C (en mm)	tube polyuréthane polyester calibré, en rouleau de 25 m						pour 25 m
									
3	1,8	8	1025U03 01 18						0,020
4	2,5	10	1025U04 01	1025U04 02	1025U04 03	1025U04 04	1025U04 05	1025U04 06	0,310
5	3	13	1025U05 01			1025U05 04			0,522
6	4	15	1025U06 01	1025U06 02	1025U06 03	1025U06 04	1025U06 05	1025U06 06	0,591
8	5,5	20	1025U08 01	1025U08 02	1025U08 03	1025U08 04	1025U08 05	1025U08 06	0,971
10	7	25	1025U10 01	1025U10 02		1025U10 04	1025U10 05	1025U10 06	1,467
12	8	35	1025U12 01	1025U12 02		1025U12 04	1025U12 05	1025U12 06	2,406
14	9,5	45	1025U14 01 95			1025U14 04 95			2,815




## 1100U tube polyuréthane polyester souple, rouleau de 100 m

Ø ext. tube mm	Ø int. tube mm	R rayon minima de courbure à 20° C (en mm)	tube polyuréthane polyester calibré, en rouleau de 100 m						pour 100 m
									
4	2,5	10	1100U04 01	1100U04 02	1100U04 03	1100U04 04	1100U04 05	1100U04 06	1,092
5	3	13	1100U05 01			1100U05 04			1,605
6	4	15	1100U06 01	1100U06 02	1100U06 03	1100U06 04	1100U06 05	1100U06 06	2,064
8	5,5	20	1100U08 01	1100U08 02	1100U08 03	1100U08 04	1100U08 05	1100U08 06	3,610
10	7	25	1100U10 01			1100U10 04			6,105
12	8	35	1100U12 01			1100U12 04			8,610
14	9,5	45	1100U14 01 95			1100U14 04 95			11,215

## 1025U..R tube polyuréthane polyéther souple calibré, rouleau de 25 m

Ø ext. tube mm	Ø int. tube mm	R rayon minima de courbure à 20° C (en mm)	tube polyuréthane polyéther souple calibré, en rouleau de 25 m			pour 25 m
						
4	2,5	8	1025U04R01	1025U04R04	1025U04R08	0,310
5	3	11			1025U05R08	0,522
6	4	12	1025U06R01	1025U06R04	1025U06R08	0,591
8	5,5	18	1025U08R01	1025U08R04	1025U08R08	0,971
10	7	22	1025U10R01	1025U10R04	1025U10R08	1,467
12	8	35	1025U12R01	1025U12R04	1025U12R08	2,406
14	9,5	45		1025U14R04 95	1025U14R08 95	2,815

## 1100U..R tube polyuréthane polyéther souple calibré, rouleau de 100 m

Ø ext. tube mm	Ø int. tube mm	R rayon minima de courbure à 20° C (en mm)	tube polyuréthane polyéther souple calibré, en rouleau de 100 m			pour 100 m
						
4	2,5	8	1100U04R01	1100U04R04	1100U04R08	1,092
6	4	12	1100U06R01	1100U06R04	1100U06R08	2,064
8	5,5	18	1100U08R01	1100U08R04	1100U08R08	3,610
10	7	22			1100U10R08	6,109
12	8	35			1100U12R08	8,610
14	9,5	45			1100U14R08 95	11,215