

Technical data sheet

Article number:
924-00381

RD5-3

Product Group	Ring Terminals
Product Family	Double Grip Pre-Insulated
Material	Copper (CU), Polyvinylchloride (PVC)
Colour	Yellow (YE)
Application Range	Low Voltage
Application Tool	HYYT7
Conductor Size Range mm ²	4.0-6.0 mm ²
Diameter (D)	6.8 mm
for Hole Ø (FH)	3.2 mm
Length (L)	26.2 mm
Length (L2)	13.6 mm
Length (L3)	12.6 mm
Max Current	48 A
Max Voltage	600 V
Operating Temperature	+75 °C
Package Content	100 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	9.5 mm

