Plug SLS205...

Stackable, Ø 2 mm with spring-loaded MULTILAM for self-assembly of test leads.


Solder connection.

SLS205

SLS205-X









Order No.	Туре	Rated voltage/current	Cable (A)			*Colors
22.2616-*	SLS205	30 VAC / 10 A 60 VDC / 10 A	PVC TPE Ø 2.1 mm SIL Ø 2.3 mm	0.5 mm²	Au	20 21 22 23 24 25 26 27 28 29
22.2617-*	SLS205-X	30 VAC / 10 A 60 VDC / 10 A	PVC TPE Ø 2.1 mm SIL Ø 2.3 mm	0.5 mm²	Ni	21 22 23 24 25 26 27 28 29

Component parts

22.2030-*	KT205	Insulator
22.1004	LS205	Plug for SLS205
22.5006	LS205N	Plug for SLS205-X



Assembly instructions MA134


www.staubli.com/electrical

Plug SLS2-S

In-line, rigid, \emptyset 2 mm for self-assembly of test leads.

Solder connection.







Assembly instructions MA132

www.staubli.com/electrical

Order No.	Туре	Rated voltage/current	Cable (A)			*Colors
22.2609-*	SLS2-S	30 VAC / 10 A 60 VDC / 10 A	max. Ø 2.1 mm	0.5 mm ²	Au	21 22 23 24 25 26 27 28 29

Component parts

22.2010-*	KT2-S	Insulator
22.1002	LS2-S	Plug