





	D1, D2, C1, C2; NO/NC			L1, L2, L3
	3RV1901-1	3RV1901-2		
$\varnothing 5 \dots 6 \text{ mm} / \text{PZ2}$	0,8 ... 1,2 Nm 7 to 10,3 LB.IN	----	$\varnothing 5 \dots 6 \text{ mm} / \text{PZ2}$	3 ... 4,5 Nm 27 to 40 LB.IN
	2 x 0,5 ... 1,5 mm <sup>2</sup> 2 x 0,75 ... 2,5 mm <sup>2</sup>	2 x 0,5 ... 2,5 mm <sup>2</sup>		2 x 0,75 ... 16 mm <sup>2</sup>
	2 x 0,5 ... 2,5 mm <sup>2</sup>	2 x 0,5 ... 1,5 mm <sup>2</sup>		2 x 0,75 ... 16 mm <sup>2</sup> 1 x 0,75 ... 25 mm <sup>2</sup>
----	----	----		2 x 0,75 ... 25 mm <sup>2</sup> 1 x 0,75 ... 35 mm <sup>2</sup>
<b>AWG</b>	2 x 18 to 14	2 x 18 to 14	<b>AWG</b>	2 x 18 to 3 1 x 18 to 2

3RV1901-2.

