









source images

2476TX1W

Product no.: 2476TX1W

Side cutter, same as 2476TX1 with optional safety device "wire catcher"



The jaws of the cutter have straight edges and taper to a point. This head shape allows access to difficult to reach areas but reduces the cutting capacity in comparison to the same size oval head cutter.



Series 2400 MagicSense model




W: Safety device for holding wire scraps This safety device for side cutters holds wire scraps securely ater cutting. Available for all Series 500, 600, 2400 & 2600 cutters. Order suffix "W", e.g. 595EW

The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 2400 Magic Sense is a range of medium-sized precision cutters that combines robustness, visibility and accessibility. A large variety of head shapes for precision work in hard-to-reach areas. The optimized ergonomic shape of the Series 2400 MagicSense prevents hand fatigue. These cutters are manufactured from improved induction-hardened cutting edges up to 64 – 65 HRc for an extremely long service life. The cutting edges are made from special tool steel. The precision cutters have a nonreflecting surface, are ESD safe and resharpenable.

THE PERFECT CUT

Strong, sharp and precise - every time















1	
Length mm	128
Length of cutting edges mm	10
Head width mm	11
Head thickness mm	6
Head length mm	18.5
Max. cutting capability – hard wire mm	Ø 0,4
Weight in oz	2.617
Length of cutting edges Inches	0.394
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	0.728
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	Ø 0,5
Max. cutting capability – copper wire mm	Ø 1,0
Length inches	5.039
Weight in g	74.2
Erem applications	Microelectronic

Phone: +49 (0) 7143 / 580-0 Fax.: +49 (0) 7143 / 580-108 Email: info@weller-tools.com Web: www.weller-tools.com