

53707

Tube Brush, 510 mm, Medium, Orange



This is the largest diameter of the tube cleaners. It is widely used to clean pipes, tap outlets and narrow spaces between machine parts. The filaments are attached to a twisted stainless steel rod which makes chemical resistant and strong.

Technical Data

Item Number	53707
Visible bristle length	27 mm
Material	Polypropylene Polyester Stainless Steel
Suitable for Food Contact (EU 1935/2004), DoC ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	15 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	840 Pcs
Quantity Per Layer (Pallet)	60 Pcs.
Box Length	580 mm
Box Width	385 mm
Box Height	130 mm
Product Diameter	60 mm
Length	510 mm
Width	65 mm
Height	60 mm
Gross Weight	0,12 kg
Net Weight	0,1 kg
Cubik metre	0,0022 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	80 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705020537073
GTIN-14 Number (Box quantity)	15705020537070
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its

intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact