



Shockwave HSS-G TiN Red Hex 3.2 mm - 2 pcs

RED HEX - SHOCKWAVE™ HSS-TiN METAL DRILL BITS

- Impact rated drill bit with 1/4" hex shank optimised for impact drivers.
- Titanium Nitride coating dispenses heat and makes the drill bit suitable for use also in high speed.
- QUAD EDGE™ Tip: unique combination of 135° split point and four cutting edges: 135° split point allows for precise & fast drilling start without walking. Four cutting edges create smaller chips to prevent heat build up for longer life.
- Variable flute geometry: For faster material ejection. Helps the bit run cooler and prevent it from burning out faster.
- Enhanced tapered web: Wider core towards the shank of the drill bit. Strengthens the core to increase overall flute durability.



ø (mm)	3.2
Article Number	48894706
Pack quantity	2
Total length (mm)	66.5
Working length (mm)	23