



Fuse base, high speed, 250 A, AC 690 V, 50 kA, NH1, 1P, IEC, UL, CSA



Part no. NH1 SINGLE POLE SILVER 1/4 SCREW PV
Catalog No. SD1-D-PV

Delivery program

Product range			Fuse accessory
Basic function			Fuse-base
Field of application			high speed
Rated current	I	A	250
Rated voltage			AC 690 V
Construction size			NH1
Breaking Capacity		kA	50
Number of poles			1P
usable for size/applications			NH Photovoltaic fuse links
Standard/Approval			IEC UL CSA
Material			Glass-filled PBT body
Standards/Regulations			IEC 60269-1
Optional accessories			Microswitches, Shroud kit, Phase barriers, Neutral links and Fuse extraction handle

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse base (EC000067)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Low-Voltage HRC fuse base (ecl@ss10.0.1-27-14-21-06 [AKE278013])			
Construction size			NH1
Number of poles			1
Rated current		A	250
Bus-mounting type			Yes
Swivelling mechanism			Yes

Additional product information (links)

Product datasheet (pdf)	http://www1.cooperbusmann.com/pdf/83f3f664-8ac5-440a-a778-cf342fb62327.pdf
-------------------------	---