



Product data sheet  
Power tools for trade & industry

Cordless Multi-Cutter

PRO GOP 12V-28



The most compact cordless multi-tool in the Bosch Starlock category

The most important data

Battery voltage	12.0 V
No-load rotation	5,000 – 20,000 opm
Oscillation angle on left and right	1.4 °

**Part Number** 0 601 8B5 002

Technical data

Technical data

Battery voltage	12.0 V
No-load rotation	5,000 – 20,000 opm
Oscillation angle on left and right	1.4 °
Weight excl. battery	0.81 kg
Packaging dimensions (width x length x height)	360 x 440 x 110 mm
Weight incl. battery	1 kg

Noise/vibration information

Grinding

Vibration emission value ah	2.9 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

Sawing with plunge-cutting saw blade

Vibration emission value ah	9.2 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

Sawing with segment saw blade

Vibration emission value ah	2.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

Scraping

Vibration emission value ah	8.3 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

---

## Advantages:

- Lightweight design for comfortable handling and convenience of use
- Smallest handle grip makes it very ergonomic and easy to operate
- Superior Starlock interface of optimised 3-dimensional tight connection for highest direct power transfer

**HEAVY  
DUTY**



---

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

