

## Features

- Lightweight and flexible
- European Standard EN559
- Available in blue and red colour options
- 25m length

## RS PRO Hose Pipe

RS Stock No.: [486-473](#), [486-479](#), [486-489](#)

[486-518](#), [486-502](#), [486-463](#)



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

**Product Description**

Lightweight and flexible, smooth, blue hose for oxygen. Manufactured up to European Norm EN ISO 3821:2019. It's designed to be used with industrial autogenic welding equipment, usually together with red acetylene hose. Also it is ideal for natural gas and air.

**General Specification**

Brand	RS PRO
Features	Flexible
Materials	EPDM, SBR
Colour	Blue (486473, 486479, 486489), Red (486518, 486502, 486463)
Length	25m
Suitable Applications	Welding
Maximum Operating Temperature	+80°C
Minimum Operating Temperature	-30°C
Maximum Working Pressure	20 bar
Hose Pipe Action	Transfer
Standards Met	ISO 3821
Bend Radius	100mm

**Products in series**

Stock No.	Lenght	Inner Diameter	Outer Diameter	Colour
486-473	25m	6,3mm	13,3mm	Blue
486-479	25m	8mm	14,6mm	Blue
486-489	25m	10mm	17mm	Blue
486-518	25m	6,3mm	13,3mm	Red
486-502	25m	8mm	14,6mm	Red
486-463	25mm	10mm	17mm	Red

**Similar Products**

Stock No.	Lenght	Inner Diameter	Outer Diameter	Colour
486-570	25m	6,3mm	13,3mm	Orange
486-580	25m	8mm	14,6mm	Orange
486-586	25m	10mm	17mm	Orange