

LED system light



Product-Nr. 155410-01

EAN: 4260556627090

Model: SYSTEMLED EVO - POWER Daylight White

Order number: 155410-01

Model: SYSTEMLED EVO - POWER Daylight White

Type: LED system light

Illuminant: SMD LED

Total output incl. driver: ~80 W

Power consumption: ~73 W

Lamp luminous flux: 13000 lm

Lamp luminous efficiency: 184 lm/W

Light distribution: direct

Light colour: 5700K 3-step MacAdam

R9: 90

Connected load: 120-277VAC, 50 - 60 Hz

Power supply: integrated

Connection (connector): Wieland GST18

Degree of protection: IP40

Class of protection: I

Glare control: Microprisms

Beam angle (optics): 90°

Operating temperature: -10 °C - +50 °C (14 °F - 122 °F)

Storage temperature: -20 °C - +80 °C (-4 °F - 176 °F)

Colour rendering (Ra): >90 (typ. 95)

Lamps lifetime: > 100,000 h (L80/B10)

Housing material: aluminum and PMMA

Height [B] x Width [C]: 48 mm x 139 mm (~1,89" x ~5,47")

Length [A]: 1782 mm (~70,16")

Mounting: T-slot rear (8 mm)

Weight (net): 4750 g (~168 oz)

Gross weight: 6630 g (~234 oz)

Risk group (DIN EN 62471): free group

Markings: CE, UKCA

Dimmable: yes

Mounting accessories: optional

Made in: Germany

Feature: externally dimmable/switchable

