

FEATURES

- Display type LED indicator
- Length for test is from 1m to 350m
- RJ5, Tact switch keypad
- Alkaline 9VDC battery type
- Open and short error status

RS PRO LAN Test Equipment of Tracer

RS Stock No.: 136-8578



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO test kit 3-IN-1 tool that contains tracer, toner and cable tester with a remote terminator.
Includes :BNC to F female test cable
BNC to female test cable
Screw, Nylon bag, User's Manual

General Specifications

Cable Type	BNC, F
Test Type	Tracer
Connector	RJ45, Alligator Clip(Red, Black), BNC connector
Display Type	LED
Tone	Yes
Operating Way	Tact Switch Keypad
Body Material	Plastic Tracer
Application	SCADA engineering and system integration, Industrial automation, Network engineering, Service and maintenance, Field services

Electrical Specifications

Power Source	Battery
Battery Type	9V

Mechanical Specifications

Dimensions	Amplifier Probe : 230(L)mm x 60.3(W)mm x 28(H) mm Tone Generator : 104(L)mm x 70(W)mm x 36(H) mm
Length	Amplifier Probe -230mm,Tone Generator-104mm
Width	Amplifier Probe -60.3mm,Tone Generator-70mm
Height	Amplifier Probe- 28mm,Tone Generator- 36mm

Operation Environment Specifications

Maximum Operating Temperature	50°C
Minimum Operating Temperature	0°C
Storage Temperature	-10°C to 60°C
Humidity	10 % to 90 % non-condensing

Approvals

Compliance/Certifications	CE approval
---------------------------	-------------

