

Rittal – The System.

Faster – better – everywhere.

TopTherm air/air heat exchanger wall-mounted with controller – SK 3130.100

Date : Apr 26, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TopTherm air/air heat exchanger wall-mounted with controller – SK 3130.100

created: 26.04.2021 build on www.rittal.com/uk-en



Product description

Description:	Air/air heat exchangers are particularly well-suited to aggressive ambient conditions, because the internal and external air circuits are completely separate from one another.
Colour:	RAL 7035
Protection category IP to IEC 60 529:	Internal circuit IP 54 External circuit IP 34
Supply includes:	Complete unit ready for connection Plug-in terminal strip Floating fault signal contact in case of overtemperature Drilling template Assembly parts

Product description

Specific thermal output:	90 W/K
Air throughput (unimpeded air flow):	External circuit with 50 Hz: 850 m³/h External circuit with 60 Hz: 945 m³/h Internal circuit at 50 Hz: 850 m³/h Internal circuit at 60 Hz: 945 m³/h
Rated operating voltage:	230 V, 1~, 50 Hz/60 Hz
Dimensions:	Width: 400 mm Height: 1580 mm Depth: 215 mm

Temperature control:	Electronic control with digital display (factory setting +35 °C)
Temperature range:	Operation (environment): -5 °C...+55 °C
Rated current max.:	At 50 Hz: 1.35 A At 60 Hz: 1.8 A
Miniature circuit-breaker/fuse:	4 A
eCl@ss 8.0/8.1:	27180711
Packs of:	1 pc(s).
Weight/pack:	34 kg
EAN:	4028177388994
Customs tariff number:	84158300
ETIM 7.0:	EC002514
ETIM 6.0:	EC002514
eCl@ss 8.0/8.1:	27180711
eCl@ss 6.0/6.1:	27180711
Product description:	SK Air/Air heat exchanger TopTherm, wall-mounted with controller, 90 W/K, 230 V, 1~, 50/60 Hz, WHD: 400 x 1580 x 215 mm
Approvals	
Approvals:	Approval overview UR + C-UR
Certificates:	EAC
Declarations:	Declaration of conformity