

gF/aG residential-use fuses

10.3 x 31,5 - 400 V



Size	Current (A)	Voltage (V)	Ref. number w/o indicator	Cat.number w/o indicator	Ref. number with indicator	Cat.number with indicator	Pckg
10,3 x 31,5	16	400	L216141J	FR1031GG40V16	A201802J	FR1031GG40V16I	10
10,3 x 31,5	20	400	J216645J	FR1031GG40V20	X211022J	FR1031GG40V20I	10
10,3 x 31,5	25	400	W217162J	FR1031GG40V25	P211544J	FR1031GG40V25I	10

NF C 61-203 compliant and marked; the other fuse ratings are not mentioned in the standard. mentionnés dans la

8.5 x 36 - 400 V



Size	Current (A)	Voltage (V)	Ref. number w/o indicator	Cat.number w/o indicator	Ref. number with indicator	Cat.number with indicator	Pckg
8,5 x 36	2	400	A217672J	FR836GG40V2	N212578J	FR836GG40V2I	10
8,5 x 36	4	400	K218187J	FR836GG40V4	Y213093J	FR836GG40V4I	10
8,5 x 36	6	400	Y218705J	FR836GG40V6	R213593J	FR836GG40V6I	10
8,5 x 36	10	400	L219223J	FR836GG40V10	T214101J	FR836GG40V10I	10
8,5 x 36	16	400	N219754J	FR836GG40V16	X214610J	FR836GG40V16I	10
8,5 x 36	20	400	W222199J	FR836GG40V20	E215123J	FR836GG40V20I	10
8,5 x 36	25	400	R222954J	FR836GG40V25	G215631J	FR836GG40V25I	10
8,5 x 36	32	400	A200744J	FR836GG40V32	N216143J	FR836GG40V32I	10

10.3 x 38 - 400 V



Size	Current (A)	Voltage (V)	Ref. number w/o indicator	Cat.number w/o indicator	Ref. number with indicator	Cat.number with indicator	Pckg
10,3 x 38	25	400	P201286J	FR1038GG40V25	L216647J	FR1038GG40V25I	10
10,3 x 38	32	400	Z201801J	FR1038GG40V32	Y217164J	FR1038GG40V32I	10

NF C 61-203 compliant and marked; the other fuse ratings are not mentioned in the standard.



Action du voyant

Functions

Fuse for residential use (housing, apartment buildings).

Applications

General protection for lines, socket outlets, lamps, heating systems, household appliances. Household power boxes, new or renovations.

MSD fuse holders and carriers



Fuse Size	Single-pole w/o indicator 1 module		Single-pole with indicator 1 module		Single-pole+N w/o indicator 1 module		Single-pole+N with indicator 1 module	
8,5 x 23	C217674K	MSD8231	A218707K	MSD8231	N219225K	MSD8231N	T222956K	MSD8231NI
10,3 x 25,8	R201288K	MSD10251	Y211023K	MSD10251I	Q211545K	MSD10251N	Z213094K	MSD10251NI
8,5 x 31,5	V214102K	MSD8311	F215124K	MSD8311	H215632K	MSD8311N	Z217165K	MSD8311NI
10,3 x 31,5	N218190K	MSD10311	P219226K	MSD10311	R219757K	MSD10311N	V222957K	MSD10311NI
10,3 x 38	S201289K	MSD10381	Z211024K	MSD10381	R211546K	MSD10381N	A213095K	MSD10381NI

Packaging: 12 pieces

For further information on our residential fuse lines, consult our complete technical catalog The Advisor on CD-ROM or on our Web site at

<http://www.ferrazshawmut.com/fr/products/index.htm>

under the heading **Special Purpose fuses**

> European fuses

> residential fuses