

ST40 - BizTex Microporous Coverall Type 5/6

Collection: Biztex™ Micro

Range: BizTex™

Shell Fabric: BizTex Microporous
60g

Product information

The spacious design guarantees a good fit and will not limit job performance. Made up of millions of polyethylene fibres that are spunbonded giving an excellent barrier, toughness and strength in all directions. Elasticated hood, ankles, cuffs and waist, along with a two-way front zip and sealable front flap.

Standards

EN 13034 Type 6B
EN ISO 13982 Type 5B
EN 1073-2
EN 14126
ANSI/ISEA 101
EN 1149 -5



Biztex™ Micro

Portwest's BizTex Micro fabric is a polypropylene substrate with anti-static properties. The outer layer prevents the passage of liquid molecules inwards yet allows the vapour molecules on the inside to permeate. This technology keeps the wearer fresh and comfortable.

BizTex™

All protective garments under the heading of PPE (Personal Protective Equipment) are controlled in Europe under CE Directive 89/686/EEC. Portwest has an extensive range of clothing that complies with Category 3 of this directive.

Features

- CE-CAT III
- Elasticated hood, ankles, cuffs and waist
- Two-way front zip and sealable front flap
- Low linting construction for minimal contamination
- Excellent liquid and particulate barrier protection
- Two-way zip for quick and easy access
- Ergonomically shaped hood for a perfect fit
- CE certified
- Hood for added protection against the elements



Colours

	Short	Reg	Tall	XTall
White	S - 3XL			

PORTWEST[®]

PRODUCT SPECIFICATION & TECHNICAL DATA

ST40 - BizTex Microporous Coverall Type 5/6

Commodity Code: 6210109800

Test House

Centro Tessile Cotoniero e Abbigliamento S.p.A (Notified Body No.: 0624)

Piazza S.Anna 2

, Italy

Cert No: 0771190412-00-00

Wash care



CARTON DIMENSIONS/WEIGHT

Item	Colour	Len	Wid	Hgt	Weight (Kg)	Cubic (m ³)	EAN13	DUN14
ST40WHR5	White	56.0	30.0	38.0	10.8000	0.0638	5036108133277	15036108668851
ST40WHRM	White	56.0	30.0	38.0	10.9000	0.0638	5036108133284	15036108668844
ST40WHRL	White	56.0	30.0	38.0	10.9000	0.0638	5036108133291	15036108668837
ST40WHRXL	White	56.0	30.0	38.0	10.9000	0.0638	5036108133307	15036108668868
ST40WHRXXL	White	56.0	30.0	38.0	11.1400	0.0638	5036108133314	15036108668875
ST40WHRXXXL	White	56.0	30.0	38.0	11.7000	0.0638	5036108133321	15036108732453