




**Part Number :** [2195620015](#)  
**Product Description :** EXTreme Guardian HD  
Right-Angle Plug Assembly with Guide Pins, 5  
Power Circuits, 15 Signal Circuits  
**Series Number :** 219562  
**Status :** Active  
**Product Category :** Board-to-Board  
Connectors



## Documents & Resources

**Drawings**  
[2195620015\\_sd.pdf](#)

**3D Models and Design Files**  
[2195620015\\_stp.zip](#)

**Specifications**  
[2141130000-PS-000.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                   |
|--------------------|---------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                      |
| China RoHS         |                                                   |
| EU ELV             | Not Relevant                                      |
| Low-Halogen Status | Low-Halogen per                                   |
| REACH SVHC         | Not Contained per D(2024)6225-DC<br>(07 Nov 2024) |
| EU RoHS            | Compliant per EU 2015/863                         |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474  
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

|                |                                                                                                     |
|----------------|-----------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                              |
| Category       | Board-to-Board Connectors                                                                           |
| Series         | 219562                                                                                              |
| Description    | EXTreme Guardian HD Right-Angle Plug Assembly with Guide Pins, 5 Power Circuits, 15 Signal Circuits |
| Application    | Board-to-Board, Power, Signal                                                                       |
| Component Type | PCB Header                                                                                          |
| Product Name   | EXTreme Guardian HD                                                                                 |
| UPC            | 196823042461                                                                                        |

#### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

#### Electrical

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 130.0A |
| Voltage - Maximum             | 125V   |

#### Physical

|                                |       |
|--------------------------------|-------|
| Breakaway                      | No    |
| Circuits (Loaded)              | 20    |
| Circuits (maximum)             | 20    |
| Color - Resin                  | Black |
| Durability (mating cycles max) | 200   |
| First Mate / Last Break        | No    |
| Flammability                   | 94V-0 |
| Glow-Wire Capable              | No    |
| Guide to Mating Part           | Yes   |

|                                |                                |
|--------------------------------|--------------------------------|
| Keying to Mating Part          | None                           |
| Lock to Mating Part            | None                           |
| Mated Height                   | 12.74mm                        |
| Material - Metal               | High Conductivity Copper       |
| Material - Plating Mating      | Gold                           |
| Material - Plating Termination | Tin                            |
| Material - Resin               | Liquid Crystal Polymer         |
| Net Weight                     | 27.647/g                       |
| Number of Rows                 | 1, 5                           |
| Orientation                    | Right Angle                    |
| Packaging Type                 | Tray                           |
| PC Tail Length                 | 2.53mm, 3.30mm                 |
| PCB Locator                    | Yes                            |
| PCB Retention                  | Yes                            |
| PCB Thickness - Recommended    | 1.58mm                         |
| Pitch - Mating Interface       | 5.78mm, 2.00mm                 |
| Plating min - Mating           | 0.762µm                        |
| Plating min - Termination      | 2.540µm                        |
| Polarized to Mating Part       | Yes                            |
| Polarized to PCB               | Yes                            |
| (p)ower-(s)ignal Configuration | 5p - 15s                       |
| Temperature Range - Operating  | -40° to +125°C, -40° to +105°C |
| Termination Interface Style    | Through Hole - Compliant Pin   |

---

## Mates With / Use With

### Mates with Part(s)

| Description                                                                                                    | Part Number       |
|----------------------------------------------------------------------------------------------------------------|-------------------|
| EXTreme Guardian HD Vertical Receptacle Assembly with Guide Receivers, 5 Power Circuits, 15 Signal Circuits    | <u>2195630015</u> |
| EXTreme Guardian HD Right-Angle Receptacle Assembly with Guide Receivers, 5 Power Circuits, 15 Signal Circuits | <u>2195640015</u> |

---

