



M18 FUEL™

## M18 FHX-OX

### M18 FUEL™ 4-MODE 26 MM SDS-PLUS HAMMER WITH FIXTEC™

- The fastest drilling rotary hammer in its class leading to increased productivity
- Powerful hammer mechanism delivers 2.5 J of impact energy
- Drills up to 125 ø10 x 50 mm holes on a M18™ HIGH OUTPUT™ 5.5 Ah battery charge
- AUTOSTOP™ shuts down the tool to protect the user of sharp movement in bind up situations
- FIXTEC™ system for keyless chuck changing between SDS-Plus and 13 mm metal chuck
- All metal gear case - optimum seating of the gears for enhanced tool life
- 4-mode operation: rotary hammer, hammer only, rotation only and selectable work position of the chisel (variolock) for maximum versatility
- Compatible with M18 FCDDEXL or M18 FDDEXL dust extractors
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



/// REDLITHIUM™

Blow energy (EPTA)(J)	2.5
Max. percussion rate (bpm)	4,800
Max. drilling wood/ steel/ concrete (mm)	28/ 13/ 26
Vibration drilling (m/s <sup>2</sup> )	15.9
Vibration chiseling (m/s <sup>2</sup> )	14.2
Weight with battery pack (EPTA) (kg)	4.4 (M18 HB5.5)
Kit included	No batteries supplied, No charger supplied, HD Box
Article Number	4933478888