



Product data sheet

Power tools for trade & industry

Cordless Rotary Hammer with SDS plus

PRO GBH 18V-18



Compact 18V rotary hammer with KickBack Control

The most important data

Battery voltage	18.0 V
Impact energy	1.5 J
Drilling dia. in concrete with hammer drill bits	4 – 18 mm

Part Number 0 611 927 000

Technical data

Technical data

Impact energy	1.5 J
Battery voltage	18.0 V
Weight excl. battery	1.6 kg
Tool holder	SDS plus
Packaging dimensions (width x length x height)	210 x 300 x 130 mm
BITURBO	No
Impact energy nominal	1.5 J

Drilling range

Drilling dia. in concrete with hammer drill bits	4 – 18 mm
Opt. app. range in concrete with hammer drill bits	6 – 10 mm

Drilling range

Drilling dia. in concrete with hammer drill bits	4 – 18 mm
Opt. app. range in concrete with hammer drill bits	6 – 10 mm

Noise/vibration information

Hammer drilling in concrete

Vibration emission value ah	18.7 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Kickback Control increases user's protection from injuries by stopping the motor in the event of sudden tool rotation
- High working comfort thanks to lightweight and compact design, delivering full performance with just an 18V 2.0 Ah battery
- Vibration Control reduces tool vibrations for enhanced user comfort and protection, thanks to vibration-absorbing pulsation
- Continuous power output and constant speed thanks to robust brushless motor



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

