

Technical data sheet

Article number:
151-01170

MCMB4

Product Group	Cable tie mounts for food industry, detectable
Product Family	MCMB-Series, screwable
Material	Polyamide 6.6, metal detectable (PA66MD)
Colour	Blue (BU)
CE Certification	No
Fixation Method	Screw Mount
Flammability	UL 94 HB
for Hole Ø (FH)	4.0 mm
Height (H)	4.7 mm
Length (L)	28.0 mm
Mounting Screw Type	#8 (M4) Screw
Operating Temperature	-40 °C to +85 °C
Package Content	100 pcs.
Package Content packed in	pack
ROHS compliant	Yes
UV-Stabilised	No
Width (W)	28.0 mm

HF ✓

RoHS ✓