



**MADE IN
GERMANY**



Product number 1153680100
EAN 4007123654482

DESCRIPTION

- Splash-proof housing made of a special rubber compound for continuous use.
- Extremely robust, impact-resistant, resistant to ageing and weathering.
- Resistant to various oils, greases, petrol and acids, UV and ozone radiation.
- Temperature resistance of the housing -30 °C to +80 °C.
- Quality sockets in accordance with VDE 0620-2-1.
- Sturdy metal carrying handle.
- Oil-resistant rubber cable for permanent outdoor use.
- 3 protective contact sockets 230 V with self-closing lids.

TECHNICAL DATA

Cable quality	Rubber-Neoprene	CEE 400 V / 16 A / 3P+N+PE (5p) Steckdosen	3
Cable length	1 m	Earthed socket outlets	3
Cable designation	H07RN-F 5G1,5	Plug system socket	Type F (Protective contact)
Cable colour	black	Supply/ connection option	Supply cable with plug
Max. current carrying capacity	16 A	Plug system plug	CEE 16 A 3P+N+E (5p) 400 V
Residual current circuit breaker (RCCB)	Without	Degree of protection (IP)	IP44
Protection	Without		

PACKAGING, DIMENSIONS AND WEIGHTS

Packaging	Neutral carton	Dimension LxWxH (without packing)	26 cm x 26 cm x 17 cm
UP	1	Weight of product (including packaging)	1.76 kg
Weight of product (without packaging)	1.75 kg	Dimension LxWxH (incl. packing)	26 cm x 26 cm x 17 cm

SCOPE OF DELIVERY

Compact power distributor BSV 3 LS E/16 2 IP44