

Classic ECO R63

CLECO R63 240V 28W 30° E27 SV1

0023125



Range Features

- 1:1 replacement of Incandescent reflector lamps
- More efficient - more savings
- Excellent colour rendering (CRI = 100)
- Instant illumination
- Crisp light output
- Less heat generation than incandescent lamp
- Less CO2 emissions
- Identical shape as standard incandescent lamp
- Commercial and domestic application
- Suitable for shop windows, displays, discos and clubs as well in the home
- For use in track or surface mounted spotlights or in recessed down lights
- 100% dimmable
- Average rated life 2000 hrs - two times more average life compared to incandescent lamps



PRODUCT OVERVIEW

Lamp finish	Aluminium
Lamp shape	Reflector
Colour temperature (K)	2800
CRI (Ra)	100
Dimmable	Yes
EAN code	5410288231259
Energy class	D
Equivalent watt (W)	No
Cap/Base	E27
Beam angle(°)	30
Type	R63
Watt (Nominal) (W)	28
Light colour	828 Homelight
Ordering number	0023125
Average life (Rated) (h)	2000
Luminous flux (Rated) (lm)	150
Technology	Halogen
Voltage (V)	240

DATA TABLE

General data

Average life (Nominal) (h)	2000
Control gear required	No

Classic ECO R63

CLECO R63 240V 28W 30° E27 SV1

0023125

Lamp finish	Aluminium
Lamp shape	Reflector
Dimmable	Yes
EAN code	5410288231259
Energy class	D
Energy saving lamp	No
Fixture rating	Open
General application	Residential & Consumer;Hospitality;
IEC Reference	IEC 60357
IEC Reference 2	IEC 60432-3
IEC Reference 3	IEC 60630
Intended purpose	General lighting
Cap/Base	E27
Lamp mercury content (mg)	0
Type	R63
No. of switching cycles before premature failure (min)	> 8000
Ordering number	0023125
Range features	1:1 replacement of Incandescent reflector lamps
	More efficient - more savings
	Excellent colour rendering (CRI = 100)
	Instant illumination
	Crisp light output
	Less heat generation than incandescent lamp
	Less CO2 emissions
	Identical shape as standard incandescent lamp
	Commercial and domestic application
	Suitable for shop windows, displays, discos and clubs as well in the home
	For use in track or surface mounted spotlights or in recessed down lights
	100% dimmable
	Average rated life 2000 hrs - two times more average life compared to incandescent lamps
Product name	CLECO R63 240V 28W 30° E27 SV1
Average life (Rated) (h)	2000
Special purpose lamp	No
Starting time (max) (s)	0
Technology	Halogen
Transformer required	no
Sales pack quantity	10
Warm-up time to 60% of full light (max) (s)	Instant Full Light
E-number SE	8355974
E-number FI	4740146

Classic ECO R63

CLECO R63 240V 28W 30° E27 SV1

0023125

Optical data

Colour temperature (K)	2800
CRI (Ra)	100
Beam angle(°)	30
Light colour	828 Homelight
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	150
Peak intensity (cd)	335
Luminous flux (Rated) (lm)	150
Suitable for accent lighting	Yes
Beam angle (Rated) (°)	30

Electrical data

Equivalent watt (W)	No
kWh per 1000 hours burning time	28
Lamp power factor	1
Watt (Nominal) (W)	28
Watt (Rated) (W)	28
Voltage (V)	240

Physical data

Max. Lamp Diameter (mm) - D	64
Lamp Length (mm) - C/L	105
Single packaging type	Box/Sleeve
Weight (kg)	0.03
Lamp dimension equal to filament lamp equivalent	Yes
Designed for optimum use in non standard conditions	No
Inner package net weight (kg)	0.33
Inner package dimensions (L x W x H) (cm)	32.00 x 13.50 x 11.70
Outer package dimensions (L x W x H) (cm)	69.10 x 34.20 x 24.50
Single package dimensions (L x W x H) (cm)	6.10 x 6.10 x 10.40

TECHNICAL DRAWINGS

Classic ECO R63

CLECO R63 240V 28W 30° E27 SV1

0023125

