

Specifications

Eaton 75EET

Eaton Bussmann series high speed British standard fuse, Double barrel, 75A, 690 VAC/500 VDC (IEC), 700 VAC/500 VDC (UL), Class aR, Breaking capacity 200 kA RMS Sym., 50 kA DC at 500 VDC

General specifications

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	75EET
EAN	5027590489140
UPC	051712837248
PRODUCT LENGTH/DEPTH	94 mm
PRODUCT HEIGHT	36 mm
PRODUCT WIDTH	20 mm
PRODUCT WEIGHT	91.6 g
COMPLIANCES	RoHS Compliant CE



Powering Business Worldwide

Electrical data

AMPERAGE RATING	75 A
VOLTAGE RATING	690 V (IEC), 700 V (UL)
RATED VOLTAGE AC	690 V
RATED VOLTAGE DC	500 V
INTERRUPT RATING	200 kA RMS Sym, 50 kA at 500 Vdc
CLASS	Class aR

Compatible Trip indicator/Microswitch

SUITABLE FOR	EC-600 Trip indicator kit (indicator + clips) TI700 Fuse indicator MAI Microswitch/adaptor MBI Microswitch/adaptor
--------------	---

Product specifications

APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE INDICATOR	None

Resources

BROCHURES	eaton-bussmann-series-bs88-high-speed-fuses-product-aid-pa135003en-us.pdf
CATALOGS	eaton-bussmann-series-iec-high-speed-fuses-catalogue-ca135001en-en-gb.pdf
DECLARATIONS OF CONFORMITY	eaton-high-speed-british-standard-fuse-declaration-of-conformity-uk250921en.pdf eaton-high-speed-british-standard-fuse-declaration-of-conformity-eu250043en.pdf
MCAD MODEL	eaton-hs-bs88-body-fuses-mcad-3d-models-80-56-160a-200a-fee-eet.stp

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

