

Medium-duty chemical safety gloves offering versatile chemical protection

- **Advanced defense:** AlphaTec® 58-430 medium-duty chemical-resistant gloves combine the market-leading performance of Ansell GRIP™ Technology with the flexibility and dexterity of an unlined nitrile shell
- **Heightened protection:** These nitrile gloves come in a unique, patented design that features premium-grade nitrile compound coating, providing versatile chemical protection and long-lasting snag, puncture and abrasion resistance, along with a comfortable cotton-flocked liner
- **Added safety:** In addition, AlphaTec® 58-430 solvent-resistant gloves are ideal for intermittent exposure to lubricants and cleaning agents in industrial settings

Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Chemical
- Agriculture

Applications

- Metalworking & assembly operations
- Body painting including surface inspection
- Applying sealers, touching up
- Painting or cleaning tools or robots
- Warehousing of raw materials
- Transferring liquids and solids between vessels and tanks and process equipment
- Opening furnaces draining pumps valves or lines and crackers BTX process



Key Features

- **Ansell GRIP™ Technology:** Safer handling in wet and oily conditions
- **Premium-grade nitrile coating:** Flexible chemical protection gloves
- **Solvent-resistant:** For added personal protection and safety

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Technologies



Performance Standards



0493

EN388: 2016



3001X

EN ISO 374-1:2016



JKLOPT

EN ISO 374-5:2016



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 58-430	Liner Material: N/A Coating Material: Nitrile Featured Technology: ANSELL GRIP™	7, 8, 9, 10, 11	320 / 12.6	Green	12 pairs/polybag; 12 polybags/carton; 144 pairs/carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Bldv. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.