

# TMP-UM-MAG6 - Magazine

0803329

<https://www.phoenixcontact.com/gb/products/0803329>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Magazine for THERMOMARK CARD and THERMOMARK PRIME, to hold UM material (UM3-TM)



## Commercial data

|                                      |                    |
|--------------------------------------|--------------------|
| Item number                          | 0803329            |
| Packing unit                         | 1 pc               |
| Minimum order quantity               | 1 pc               |
| Sales key                            | BG122Z             |
| Product key                          | BG122Z             |
| Catalog page                         | Page 39 (C-3-2019) |
| GTIN                                 | 4055626028194      |
| Weight per piece (including packing) | 392.3 g            |
| Weight per piece (excluding packing) | 392.3 g            |
| Customs tariff number                | 84439990           |
| Country of origin                    | DE                 |

## Technical data

### Product properties

|              |          |
|--------------|----------|
| Product type | Magazine |
|--------------|----------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 114 mm  |
| Height | 116 mm  |
| Depth  | 11.5 mm |

### Material specifications

|                |     |
|----------------|-----|
| RoHS compliant | yes |
|----------------|-----|

### Environmental and real-life conditions

#### Ambient conditions

|                                |                                 |
|--------------------------------|---------------------------------|
| Recommended storage conditions | 20 °C / 50 % relative humidity. |
|--------------------------------|---------------------------------|

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 19140615 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001675 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 43211600 |
|-------------|----------|

## Environmental product compliance

### EU RoHS

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|-----------------------------------------|-------------------------------------------------------------------------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)