



Membrane for cable entrance FL21 with 25 entrances 3x30mm + 6x18mm + 16x14mm.

Local distributor code: 398240006

0006 NSYAECPFLA25

EAN Code: 3606480389795

Main

Range	PanelSeT	
Product or component type	Cable entry membrane	
Accessory / separate part category	Cable management accessory	
Device application	Multi-purpose	
Range compatibility	PanelSeT PanelSeT S3D compact enclosure PanelSeT PanelSeT CRN compact enclosure PanelSeT PanelSeT SF suitable enclosure	
Quantity per set	Set of 1	

Complementary

Mounting support	Cable gland plate Body of enclosure	
Material	TPE (thermoplastic elastomer) SBS (styrene butadiene styrene) PP (polypropylene) SEBS (styrene ethylene butylene styrene)	
Pulling force	20 daN	
Total cable entry number	25	
Cable entry number	16 x 14 mm 6 x 18 mm 3 x 30 mm	
Height	25 mm	
Width	215 mm	
Depth	86 mm	
Colour	Light grey (RAL 7035)	
Product weight	0.306 kg	

Environment

IP degree of protection	IP65	
Standards	ASTM G154 - 06 EN 50262	
Ambient air temperature for operation	-4085 °C	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	4.000 cm
Package 1 Width	8.000 cm
Package 1 Length	22.500 cm
Package 1 Weight	311.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	25
Package 2 Height	20.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.118 kg

Logistical informations

Country of origin

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No