

Datasheet

RS Pro Stainless Steel Countersunk Head Machine Screws, M4 x 8mm

RS Stock No: **914-1787**



Product Details

RS Pro machine screw measuring M4 x 8 mm, is made of type 304 S15 A2 grade 18/8 stainless steel. The countersunk head screw with metric thread, can be used at up to 800°C. The cross drive screw is suitable for use in food, medical, chemical, construction and electronic applications.

Features and Benefits

- Countersunk head screw, metric thread
- A2 grade 18/8 stainless steel (Type 304 S15) construction
- Can be used up to 800°C
- Suitable for use in most food, medical, chemical, construction and electronic applications

**Specifications:**

Drive Type	Pozidriv
Finish	Plain
Head Shape	Countersunk
Material	Stainless Steel
Length	8 mm
Stainless Steel Type	304 (A2)
Thread Pitch	0.7
Thread Size (Metric)	M4
Head Diameter	8.04 to 8.4 mm
Head Height	2.7 mm
Recess Diameter	2.06 to 2.51 mm
Specification	DIN 965