

## EXAWATT15 – ref 798752

# Portable Power Station 1536Wh / 1800W



### Product Overview

- Multi-purpose portable power station
- Can be used to power corded tools up to 1800W, small jobsite equipment, and recharge power tool batteries.

### Product Benefits

- **1800W Output Power:** Allows you to power chargers, lighting, and appliances consuming up to 1800W (circular saw, hammer drill, microwave, kettle).
- **1536Wh LFP Battery:** LFP technology ensures a long lifespan (minimum 3000 charge/discharge cycles).
- **Robust and very easy to use**

### Technical Specifications

#### GENERAL SPECIFICATIONS

- Battery energy: 1536Wh (25.6V – 60Ah)
- Battery type: LFP Lithium Iron Phosphate (80% of the initial capacity available after 3000 full charge & discharge cycles)
- 230V inverter: 1800W pure sine wave
- Peak power: 2200W
- Integrated lighting: 4W
- EPS Mode (Emergency Power System)
- Display: LCD screen showing remaining battery %, charging and discharging power
- Operating temperature: Discharging: -20°C / +60°C  
Charging: 0°C / +50°C
- Dimensions (LxWxH) : 390\*243\*313 mm
- Weight: 17.25 kg

#### CHARGING METHODS

- AC mains: Cable supplied (1 hour)
- Solar panel: Not supplied — up to 600W max (Solar panel Voc: 12–80V)

#### OUTPUTS

- AC 230V outlets ×2: 1800W total
- 12V DC cigarette lighter socket ×1: 120W max
- USB-A fast charging ×1: 5V / 18W max
- USB-C ×1: up to 100W max

Compatible Solar Panels: 160W (#39209), 200W (#39210), 315W (#39211), 400W (#39212), 200W (39255), 440W (798770)

### Logistics

|                  |                     |
|------------------|---------------------|
| EAN              | 3545417987522       |
| Packaging height | 40,5 cm             |
| Packaging length | 48,3 cm             |
| Packaging width  | 37,2 cm             |
| Packaging weight | 19,80 kg            |
| Packaging type   | Kraft cardboard box |
| PCB              | 1                   |
| Customs code     |                     |