

Specifications for BMP41/BMP51/BMP53 Labelmaker Labels

Adhesive	Permanent Acrylic
Application	Automation & Electrical Component Markers; Bin & Storage Identification; General & Industrial Identification; Product Identification; Voice & Data Communication
Approval/Compliance	UL Recognised; CSA Accepted
Article No.	131576
Brady Material No.	B-422
Material Type	Polyester
Brand	ToughBond™ Series
Colour	Black on White
Finish	Gloss
Max. Service Temp. °C	100
Order Reference	M-90-422
Printer Compatibility	BMP41; BMP51; BMP53
Shape	Rectangle
Size - Height (mm)	38.10
Size - Width (mm)	19.05
Additional Information	Stick-on Individual Labels
Total Qty per Pack	180 Label(s) / Box
Voice/Data Application	Faceplate & Outlet; Data Centre Equipment; Bay, Rack & Frame Labels
Industry	Data & Telecommunications; Electrical; Facility & Safety Industry; General Industry; Manufacturing; Process
Min. Service Temp. °C	-40
QTY. per Row	1
Thickness (mm)	0.1016