



JUMPER3 S3 SRC

CONSTRUCTION

High-cut shoe with robust construction for optimum durability

Foot protection



Specific benefits



Comfort

- Stabilisation of the foot when walking
- Shock-absorbing heel to relieve joint strain
- Dual-density outsole



Performance

- Ladder side grip: sole design for good grip on ladders
- High stability ensured by the sole's grip properties



Hygiene

- Removable insock for easy cleaning

Certifications and norms



EN ISO 20345

S3 WRU FO A E SRC

Applications

- Public works
- Building
- Finishing works / Craftsmanship
- Events & scenic
- Manufacturing/Transformation
- Accommodation & Food services

Protects against risks



Antistatic



Shock



Slip



Perforation



Foot protection

JUMPER3 S3 SRC

CONSTRUCTION

High-cut shoe with robust construction for optimum durability

Standards - Details

Technical details

Shoe type	High shoe
Outsole material	PU, 2d
Anti-perforation insert	Stainless steel
Upper material	Leather
Safety toe-cap	Stainless steel
Lining material	Textile, Mesh polyamid
Footbed material	EVA, Polyester
Footbed characteristic	Removable, Breathable, Pre-molded
Outsole finition	Injected
Weight (g per shoe)	582
Size range	36 → 48



JUMPER3 S3 SRC

CONSTRUCTION

High-cut shoe with robust construction for optimum durability

Safety footwear

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
JUMP3S3NO36	Black	36	JUMPER3 S3 SRC	3295249241841	13295249241848	10	1	13.26 kg	43.5 cm	59.5 cm	34.0 cm
JUMP3S3NO37	Black	37	JUMPER3 S3 SRC	3295249241865	13295249241862	10	1	13.56 kg	43.5 cm	59.5 cm	34.0 cm
JUMP3S3NO38	Black	38	JUMPER3 S3 SRC	3295249241872	13295249241879	10	1	13.87 kg	43.5 cm	59.5 cm	34.0 cm
JUMP3S3NO39	Black	39	JUMPER3 S3 SRC	3295249241889	13295249241886	10	1	14.19 kg	43.5 cm	59.5 cm	34.0 cm
JUMP3S3NO40	Black	40	JUMPER3 S3 SRC	3295249241896	13295249241893	10	1	14.52 kg	43.5 cm	59.5 cm	34.0 cm
JUMP3S3NO41	Black	41	JUMPER3 S3 SRC	3295249241902	13295249241909	10	1	16.0 kg	34.8 cm	43.8 cm	60.4 cm
JUMP3S3NO42	Black	42	JUMPER3 S3 SRC	3295249241919	13295249241916	10	1	15.7 kg	47.0 cm	64.5 cm	36.5 cm
JUMP3S3NO43	Black	43	JUMPER3 S3 SRC	3295249241926	13295249241923	10	1	16.05 kg	47.0 cm	64.5 cm	36.5 cm
JUMP3S3NO44	Black	44	JUMPER3 S3 SRC	3295249241933	13295249241930	10	1	16.41 kg	47.0 cm	64.5 cm	36.5 cm
JUMP3S3NO45	Black	45	JUMPER3 S3 SRC	3295249241940	13295249241947	10	1	16.78 kg	47.0 cm	64.5 cm	36.5 cm
JUMP3S3NO46	Black	46	JUMPER3 S3 SRC	3295249241957	13295249241954	5	1	8.77 kg	25.5 cm	69.5 cm	38.0 cm
JUMP3S3NO47	Black	47	JUMPER3 S3 SRC	3295249241964	13295249241961	5	1	8.97 kg	25.5 cm	69.5 cm	38.0 cm
JUMP3S3NO48	Black	48	JUMPER3 S3 SRC	3295249241971	13295249241978	5	1	9.17 kg	25.5 cm	69.5 cm	38.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height