
electrical connection box VAVE-L1-1L4-LR Part number: 566729

VAVE-LI-IL4-LK
Part number: 566729



Data sheet

Feature	Value	
Polarity protected	for operating voltage	
Additional functions	Spark arresting	
	Reduction of holding current	
Signal status display	LED	
Nominal operating voltage DC	24 V	
Surge strength	0.8 kV	
Degree of contamination	3	
Authorisation	RCM Mark	
CE mark (see declaration of conformity)	to EU directive for EMC	
Corrosion resistance classification CRC	0 - No corrosion stress	
Protection class	IP40	
Ambient temperature	-5 60 °C	
Assembly position	Any	
Product weight	33.5 g	
Terminal cross-section	0.14 mm2	
Electrical connection	Stranded wire	
Cable length	5 m	
Protective earth connection	Not available	
Mounting type	Clip	
Housing colour	Black	
Materials note	Conforms to RoHS	
Material housing	PA	