



Main

Range of product	Pilote
Box category	Medium size junction box

Complementary

Cable entry	Smooth faces
Internal height	100 mm
Internal width	100 mm
Internal depth	50 mm
Enclosure material	Thermoplastic
Cover fixing	Metal screw
Colour code	RAL 7035
Colour	Grey
Type of front cover	Plain
Enclosure mounting	Surface

Environment

IP degree of protection	IP56
IK degree of protection	IK08
Fire resistance	650 °C glow wire test
Ambient air temperature for operation	-15...60 °C
Standards	-
Product certifications	IMQ
Environmental health and issues	Halogen free
Net weight	0.113 kg

Packing Units

Package 1 Weight	0.130 kg
Package 1 Height	5.000 dm
Package 1 width	10.000 dm

Package 1 Length	10.000 dm
------------------	-----------

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
