

Multifunction Tool



Sawing, cutting, routing, sanding...
The multifunction tools from Bosch offer countless possibilities for putting DIY ideas into practice.

Features:

- Oscillation principle for versatile applications – multifunctional and precise with powerful 180 watts
- Bosch Electronic: continuously variable control of the oscillation speed by turning the setting wheel – to suit the material being worked on
- Toolholder with universal screw – fast and easy changing of all accessories with the Allen key
- Integrated connection for dust extraction

The Technology:

Oscillation

15,000–21,000 oscillations per minute at 2.8 angular degrees allow for precise working without kick-back.

Motor

The powerful 180-watt motor ensures sustained performance. Low vibrations and the adjustable electronic speed control increases convenience.

Toolholder

The accessories can be inserted into the toolholder in different positions. The positive engagement of the toolholder prevents any risk of slipping. The single-screw principle enables easy and fast accessory changes.

Connection for dust extraction

The port for connecting a vacuum cleaner allows for clean working and a clear view of the work area.



Multifunction Tools

Specifications	PMF 180 E	PMF 180 E Set
Power input	180 W	180 W
Power output	74 W	74 W
Oscillation angle on left/right	1.4°	1.4°
No-load speed	15,000 – 21,000 rpm	15,000 – 21,000 rpm
Weight	1.2 kg	1.2 kg
Bosch Electronic	✓	✓
Part number	0 603 100 001	0 603 100 003
EAN code	3 165 140 337 250	3 165 140 506 731
Comes complete with:		
AVI 93 G, sanding plate, 93 mm	✓ 2 609 256 956	✓ 2 609 256 956
ACZ 85 EB, BIM segment saw blade Wood & Metal, 85 mm	✓ 2 609 256 943	✓ 2 609 256 943
AIZ 32 EC, HCS plunge-cutting saw blade Wood, 32 x 40 mm	✓ 2 609 256 947	✓ 2 609 256 947
Sanding sheet set, red quality, 93 mm	✓ 2 609 256 957	✓ 2 609 256 957
ACZ 85 RT, HM-RIFF segment saw blade, 85 mm	–	✓ 2 609 256 952
AIZ 10 AB, BIM plunge-cutting saw blade Metal, 10 x 20 mm	–	✓ 2 609 256 951
AIZ 32 BB, BIM plunge-cutting saw blade Hard Wood, 32 x 40 mm	–	✓ 2 609 256 946
ATZ 52 SFC, HCS scraper, flexible, 52 x 45 mm	–	✓ 2 609 256 955
Allen key	✓	✓
Plastic carrying case	✓	✓